# 40 341

# **ALLURE**

# 24" TOWEL BAR



#### STANDARD SPECIFICATION:

- GROHE StarLight®
- Concealed mounting
- Metal material
- 22 <sup>2</sup>/<sub>5</sub>" center-to-center distance
- 24" length



#### **PRODUCT FEATURES:**

### GROHE StarLight®

#### **CERTIFICATIONS:**

#### **AVAILABLE FINISHES:**

40341001 GROHE StarLight® Chrome
403412431 Matte Black

40341EN1 Brushed Nickel InfinityFinish™

40341GN1 Brushed Cool Sunrise

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 04-26-2023 **US Canada** 

Tel: 1.630.582.7711 Fax: 1.630.582.7722 For the most current Specification Sheet, go to www.grohe.us.

Canada
Tel: 1.888.644.7643 Fax: 1.905.366.2071
For the most current Specification Sheet,
go to www.grohe.ca.



# 40 341

# **ALLURE**

# GROHE SPA

# 24" TOWEL BAR

#### **TECHNICAL DATA:**

Product Height 2-3/16 in

Product Length 24-5/8 in

Product Width 2-1/16 in

