

30 378

**DEFINED™**

SINGLE-HANDLE PULL DOWN DUAL  
SPRAY BAR FAUCET 1.75 GPM

Pure Freude  
an Wasser






**STANDARD SPECIFICATION:**

- GROHE SilkMove®
- GROHE StarLight®
- Pull-down dual spray with toggle function:  
switches between regular water flow and spray  
without turning off the water
- 14 5/8" Faucet height
- 8 7/16" Aerator height
- 7 5/16" Faucet reach
- SpeedClean® anti-lime system
- Forward rotation lever - does not hit  
backsplash
- 360° Swivel radius
- Solid brass body
- Flexible connection hoses
- 1.75gpm flow rate
- CALGreen compliant



**PRODUCT FEATURES:**



-  GROHE SilkMove®
-  GROHE StarLight®
-  Speed Clean®

**CERTIFICATIONS:**



- ADA
- CEC Certified
- Low Lead Certified
- CALGreen Compliant
- Massachusetts Plumbing Board Approved
- Energy Policy Act of 1992
- NSF 372
- CSA B125.1
- ASME A112.18.1
- Complies with lead plumbing laws

**AVAILABLE FINISHES:**

- 30378000**  GROHE StarLight®  
Chrome
- 30378DC0**  SuperSteel  
InfinityFinish™

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

Tel: 1.630.582.7711 Fax: 1.630.582.7722  
We reserve the right to make revisions without notice to product specifications.  
For the most current Specification Sheet, go to [www.grohe.us](http://www.grohe.us).  
06-30-2021

PART OF **LIXIL**

30 378

**DEFINED™**

SINGLE-HANDLE PULL DOWN DUAL  
SPRAY BAR FAUCET 1.75 GPM

*Pure Freude  
an Wasser*



**TECHNICAL DATA:**

|                      |                   |
|----------------------|-------------------|
| Product Height       | 14-5/8 in         |
| Product Width        | 5-1/16 in         |
| Fitting Spout Height | 8-7/16 in         |
| Fitting Spout Reach  | 7-5/16 in         |
| GPM (Min)-GPM (Max)  | 1.75 gal (US)/min |

