

24 107

GROHTHERM®

SINGLE FUNCTION 2-HANDLE THERMOSTATIC VALVE TRIM WITH CONTROL MODULE

Pure Freude
an Wasser



STANDARD SPECIFICATION:

- GROHE StarLight®
- GROHE TurboStat® compact cartridge with wax thermoelement
- Thermostatic temperature control with GROHE SafeStop safety button at 100°F/38°C
- GROHE SafeStop Plus temperature limiter at 115° F/46° C
- Volume control with ceramic disc stop valve, 120°
- 6 1/4" Metal wall trim plate with GROHE QuickFix® (concealed mounting screws)
- Metal trim angle adjustable up to 6°
- Upper handle includes integrated volume control and On/Off
- ADA compliant lever handles
- Includes service stops
- 7.1gpm at 45psi
- Requires GROHE Rapido® SmartBox (35 601 000) (sold separately)



PRODUCT FEATURES:

-  GROHE StarLight®
-  GROHE QuickFix®
-  GROHE TurboStat®

CERTIFICATIONS:

- Massachusetts Plumbing Board Approved
- N/A
- ASSE 1016
- CSA B125.1
- CSA B125.16
- ASME A112.18.1
- ASME A112.1016

AVAILABLE FINISHES:

- 24107000**  GROHE StarLight® Chrome
- 241072430**  Matte Black
- 24107A00**  Hard Graphite
- 24107EN0**  Brushed Nickel InfinityFinish™
- 24107GN0**  Brushed Cool Sunrise

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 07-06-2022

US
Tel: 1.630.582.7711 Fax: 1.630.582.7722
For the most current Specification Sheet,
go to www.grohe.us.

Canada
Tel: 1.888.644.7643 Fax: 1.905.366.2071
For the most current Specification Sheet,
go to www.grohe.ca.

PART OF **LIXIL**

24 107

GROHTHERM®

SINGLE FUNCTION 2-HANDLE
THERMOSTATIC VALVE TRIM WITH
CONTROL MODULE

*Pure Freude
an Wasser*



TECHNICAL DATA:

Product Height 158 mm

Product Length 43 mm

Product Width 158 mm

