

26 570

CONCETTO™

310 MONO SHOWER HEAD, 12" - 1 SPRAY

Pure Freude
an Wasser



STANDARD SPECIFICATION:

- GROHE StarLight®
- GROHE DreamSpray®
- GROHE EcoJoy®
- GROHE SpeedClean®
- 1 Spray: GROHE PureRain
- 12" Face
- Ball joint angle adjustable $\pm 10^\circ$
- 1/2" NPT Connection
- Recommended Rainshower™ arm: (26 632)
(sold separately)
- Max. flow rate: 1.75gpm (6.6L/min)



PRODUCT FEATURES:





-  GROHE StarLight®
-  GROHE DreamSpray®
-  GROHE EcoJoy™
-  Speed Clean®

CERTIFICATIONS:



- WaterSense
- CEC Certified
- CALGreen Compliant
- Massachusetts Plumbing Board Approved
- Energy Policy Act of 1992
- CSA B125.1
- ASME A112.18.1

AVAILABLE FINISHES:

- 26570000**  GROHE StarLight® Chrome
- 26570A00**  Hard Graphite
- 26570EN0**  Brushed Nickel InfinityFinish™
- 26570GN0**  Brushed Cool Sunrise

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 07-06-2022

US
Tel: 1.630.582.7711 Fax: 1.630.582.7722
For the most current Specification Sheet,
go to www.grohe.us.

Canada
Tel: 1.888.644.7643 Fax: 1.905.366.2071
For the most current Specification Sheet,
go to www.grohe.ca.

PART OF **LIXIL**

26 570

CONCETTO™

310 MONO SHOWER HEAD, 12" - 1
SPRAY

*Pure Freude
an Wasser*



TECHNICAL DATA:

Product Height	226 mm
Product Length	310 mm
Product Width	310 mm
GPM (Min)-GPM (Max)	1.75 gal (US)/min

