

U.S. Government

Federal law prohibits removal of this label before consumer purchase.

ENERGYGUIDE

Instantaneous Water Heater -Propane Gas
Capacity (max. flow rate):5.8 gpm

RINNAI
Model (CXP199I) REU-NBP3237FFC-US



Estimated Yearly Energy Cost

\$424



Cost Range of Similar Models

The estimated yearly operating cost of this model was not available
when the range was published.

Maximum Gallons Per Minute of Hot Water (GPM Rating)

very small	low	medium	high 5.8 gpm
------------	-----	--------	------------------------

- Your cost will depend on your utility rates and use.
- Cost range based only on models fueled by Propane Gas with a high maximum gallons per minute of hot water (4 gpm or more).
- Estimated energy cost based on a national average Propane Gas cost of \$2.23 per gallons
- Estimated yearly energy use: 189 gallons.

ftc.gov/energy

U.S. Government

Federal law prohibits removal of this label before consumer purchase.

ENERGYGUIDE

Instantaneous Water Heater -Natural Gas
Capacity (max. flow rate):5.8 gpm

RINNAI
Model (CXP199I) REU-NBP3237FFC-US



Estimated Yearly Energy Cost

\$212



Cost Range of Similar Models

Maximum Gallons Per Minute of Hot Water (GPM Rating)

very small	low	medium	high 5.8 gpm
------------	-----	--------	------------------------

- Your cost will depend on your utility rates and use.
- Cost range based only on models fueled by Natural Gas with a high maximum gallons per minute of hot water (4 gpm or more).
- Estimated energy cost based on a national average Natural Gas cost of \$1.21 per therms
- Estimated yearly energy use: 172 therms.

ftc.gov/energy