

23 794

LINEARE™

SINGLE HOLE SINGLE-HANDLE S-SIZE BATHROOM FAUCET 1.2 GPM

*Pure Freude
an Wasser*



STANDARD SPECIFICATION:

- GROHE SilkMove®
- GROHE StarLight®
- GROHE EcoJoy™
- GROHE QuickFix® Plus installation
- GROHE AquaGuide adjustable aerator 20°-40°
- 8 3/8" Faucet height (open position)
- 7 1/16" Faucet height (closed position)
- 5 1/16" Spout reach
- 4 3/4" Aerator height
- Solid brass construction with metal lever
- 23 1/2" Nylon braided flex hoses
- CALGreen/CEC compliant
- 1.2gpm (WaterSense)



PRODUCT FEATURES:


-  **GROHE StarLight®**
-  **GROHE SilkMove®**
-  **GROHE EcoJoy™**
-  **GROHE QuickFix®**

CERTIFICATIONS:



- ADA
- WaterSense
- CEC Certified
- Low Lead Certified
- CALGreen Compliant
- Energy Policy Act of 1992
- NSF 61
- NSF 372
- CSA B125.1
- ASME A112.18.1
- Complies with lead plumbing laws

AVAILABLE FINISHES:

- 2379400A**  GROHE StarLight® Chrome
- 23794A0A**  Hard Graphite
- 23794ENA**  Brushed Nickel InfinityFinish™
- 23794GNA**  Brushed Cool Sunrise

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 07-06-2022

US
Tel: 1.630.582.7711 Fax: 1.630.582.7722
For the most current Specification Sheet,
go to www.grohe.us.

Canada
Tel: 1.888.644.7643 Fax: 1.905.366.2071
For the most current Specification Sheet,
go to www.grohe.ca.

PART OF LIXIL

23 794

LINEARE™

SINGLE HOLE SINGLE-HANDLE S-SIZE BATHROOM FAUCET 1.2 GPM

Pure Freude
an Wasser



TECHNICAL DATA:

Product Height	213 mm
Product Length	192 mm
Product Width	48 mm
Fitting Spout Height	120 mm
Fitting Spout Reach	128 mm
Fitting Handle Height	180 mm
GPM (Min)-GPM (Max)	1.2 gal (US)/min
Fitting No of Holes Required	1

