

26 046

# TEMPESTA® COSMOPOLITAN

100 HAND SHOWER - 2 SPRAYS

Pure Freude  
an Wasser






## STANDARD SPECIFICATION:

- GROHE StarLight®
- GROHE DreamSpray®
- GROHE EcoJoy®
- Speed Clean® anti-lime system
- 4" Face
- 2 Sprays: Rain, Jet
- 1/2" NPT female threads
- Chrome - white spray face
- Brushed Nickel - charcoal spray face
- Max. flow rate: 1.75gpm (6.6L/min)



## PRODUCT FEATURES:



-  GROHE StarLight®
-  GROHE DreamSpray®
-  GROHE EcoJoy™
-  Speed Clean®

## CERTIFICATIONS:



- WaterSense
- CEC Certified
- CALGreen Compliant
- Massachusetts Plumbing Board Approved
- CSA B125.1
- ASME A112.18.1

## AVAILABLE FINISHES:

- 26046002**  GROHE StarLight® Chrome
- 26046EN2**  Brushed Nickel InfinityFinish™

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

Tel: 1.630.582.7711 Fax: 1.630.582.7722  
We reserve the right to make revisions without notice to product specifications.  
For the most current Specification Sheet, go to [www.grohe.us](http://www.grohe.us).  
10-20-2021

PART OF **LIXIL**

26 046

# TEMPESTA® COSMOPOLITAN

100 HAND SHOWER - 2 SPRAYS

Pure Freude  
an Wasser



## TECHNICAL DATA:

Product Height	8-1/16 in
Product Length	5-1/8 in
Product Width	3-15/16 in
GPM (Min)-GPM (Max)	1.75 gal (US)/min

