

14 469

## EUROCUBE®

# PRESSURE BALANCE VALVE TRIM WITH CARTRIDGE

Pure Freude  
an Wasser



### STANDARD SPECIFICATION:

- GROHE StarLight®
- GROHE SilkMove®
- Metal handle
- Metal trim plate with GROHE QuickFix®
- Includes pressure balance cartridge with double ceramic technology
- 5.2gpm (bottom) and 3.0gpm (top port) at 45psi (19 L/min)
- Requires GrohSafe™ 3.0 Rough-in Valve (35 110), (35 111), (35 112), (35 113), (35 114), (35 115), or (35 116) (sold separately)



### PRODUCT FEATURES:




-  GROHE StarLight®
-  GROHE SilkMove®
-  GROHE QuickFix®

### CERTIFICATIONS:



- ADA
- CSA B125.1
- ASME A112.18.1

### AVAILABLE FINISHES:

- 14469000**  GROHE StarLight® Chrome
- 14469A00**  Hard Graphite
- 14469EN0**  Brushed Nickel InfinityFinish™
- 14469GN0**  Brushed Cool Sunrise

NOTE: Install this product according to the installation guide. ADA, CSA compliant when installed to the specific requirements of these regulations.

We reserve the right to make revisions without notice to product specifications. 07-06-2022

**US**  
Tel: 1.630.582.7711 Fax: 1.630.582.7722  
For the most current Specification Sheet,  
go to [www.grohe.us](http://www.grohe.us).

**Canada**  
Tel: 1.888.644.7643 Fax: 1.905.366.2071  
For the most current Specification Sheet,  
go to [www.grohe.ca](http://www.grohe.ca).

PART OF **LIXIL**

14 469

**EUROCUBE®**

PRESSURE BALANCE VALVE TRIM WITH  
CARTRIDGE

*Pure Freude  
an Wasser*



**TECHNICAL DATA:**

**Product Height**                      **167 mm**

**Product Length**                    **57 mm**

**Product Width**                      **159 mm**

