# **MOEN**<sup>®</sup>

# **SPECIFICATIONS**

#### **DESCRIPTION**

- Metal construction with various finishes identified by suffix
- Flexible supply lines with 3/8" compression fittings
- Includes non-metal push-down waste assembly
- Includes optional 3 hole deck plate (escutcheon)

#### **OPERATION**

- Lever style handle
- Temperature controlled by 100° arc of handle travel

#### FLOW

- Water usage is limited to these maximum flow rates as indicated by the corresponding product markings
- 1.2 gpm max (4.5L/min) at 60 psi

#### CARTRIDGE

- Ceramic disc technology
- Non-metallic, non-ferrous, and brass materials
- Single body construction for easy replacement

### **STANDARDS**

- Third party certified to WaterSense,® ASME A112.18.1/CSA B125.1, and all applicable requirements referenced therein
- Certified to NSF 61/9 & 372
- Products marked with 1.2 gpm are compliant with California water efficiency regulations
- Complies with California Proposition 65 and with the Federal Safe Drinking Water Act
- ADA 🖒 for lever handles

#### WARRANTY

- Lifetime limited warranty against material or manufacturing defects to the original homeowner
- 10 year limited warranty when used in a multifamily installation
- 5 year limited warranty when used in a commercial installation
  Visit www.moen.com/support for complete details and limitations




## **FINDLAY<sup>TM</sup>**

One-Handle Lavatory Faucet

MODELS: 84516 Series



NOTE: THIS FAUCET INSTALLS THROUGH 1 HOLE, 1-1/8" (28mm) MIN. DIA.



CRITICAL DIMENSIONS DO NOT SCALE