



BG-COMMANDER-JR

JOYSTICK CONTROLLER

UNIVERSAL COMPACT SERIAL AND IP PTZ CAMERA JOYSTICK CONTROLLER (IP/RS232/422)

Introducing the BG-Commander-Jr, the compact yet powerful professional-grade joystick controller designed to meet the demands of a variety of applications. With its 2-axis joystick and zoom bridge key design, this controller provides refined control, durability, and stability, ensuring smooth and precise camera movement.

The BG-Commander-Jr sets itself apart with its 7-level PTZ speed control, providing operators with complete control over their camera movements with a visual indicator to show the current speed level. Image parameters such as exposure and gain are easily adjustable with knob-style controls and their own small displays showing current value for easy reference.



FEATURES



COMPACT DESIGN

Portable and can be strategically placed



4 COLOR LED MULTI-SCREEN DISPLAY

Review settings at a glance



SIMPLIFIED CONTROLS

Separated Pan/Tilt joystick and zoom keys for better control and reliability



CONTROL PTZ SPEEDS

7-level PTZ speed control with visual indicator



QUICK SELECT

One-button click for auto, manual, and OPT focus modes



FLEXIBLE COMPATIBILITY

Wide compatibility allows for control of most PTZ cameras



TECH SPECIFICATIONS

Communication and Control Interface

RS422/RS485 Interface	Phoenix Contact 4 pin 3.81mm Terminal
RS232C Interface	DB9 Male Interface
LAN Interface	RJ45 Female Interface
Power Supply	JEITA Type 4 Female Interface
Upgrade Online	Micro USB Female Interface

Physical and Misc.

Password Privacy Protection	YES
Kingston's Lock Holes	YES
Working Temperature	32°F ~ 104°F / 0°C ~ 40°C
Storage Temperature	-4°F ~ 140°F / -20°C ~ +60°
Working Environment	Indoor
Dimensions (L x W x H)	9.6 x 6.5 x 1.9in [244 x 164 x 48mm]
Gross Weight	2.43 lbs [1.1 kg]

Control Signal Format

0bps, 4800bps, 9600bps, 19200bps, 00bps
t
NE.
rnet Protocol:
ed Voltage DC 12V
ed Current 0.3A max
V

Camera Control and Operation

Supported number of cameras	5
Communication Protocol	VISCA, PELCO P/D, UDP
Number of LED Display	4 Units Color LED Display Screen
Number of Camera Channels	5
Variable knobs	4
Joystick	2-Axis
Zoom Mode	Tele-Wide Bridge Keys
Buttons	17 Silicon Button
Presets Short key	5 Presets per Each channel
Focus Mode	Auto / Manual / OPT
Pan/Tilt Rotation Speed	7-Level Adjustmen
Zoom In/Out Speed	7-Level Adjustmen
AE Mode / WB Mode	The mode can be switched arbitrarily, and
	the value can be adjusted

Industry-Leading Warranty & Support

BZBGEAR Pro AV products and Cameras come with a three-year warranty. An extended two-year warranty is available for our Cameras upon registration for a total of five years. We pride ourselves in our Customer Service and seven-days-a-week Tech Support.





