



BG-OMNITALK-PRO

USB/BLUETOOTH WIRELESS DESKTOP
CONFERENCE SPEAKERPHONE WITH 360 AUDIO
PICKUP UP TO 20FT

Enhance your professional communication and collaboration experiences with the BG-OMNITALK-PRO, a powerful USB Wireless Bluetooth Conference Speakerphone. Engineered to elevate your interactions, this versatile device offers seamless connectivity and cutting-edge technology, making it an essential tool for modern professionals.

Whether you're engaging in remote meetings, virtual conferences, or group discussions, the BG-OMNITALK-PRO is designed to ensure your voice is heard with clarity and precision. Embrace a new era of seamless communication as you connect, converse, and collaborate like never before.

The BG-OMNITALK-PRO is a versatile USB Wireless Bluetooth Conference Speakerphone designed for professional communication. It offers flexible connectivity options, including USB, Bluetooth, AUX, and dongle connections. Equipped with four omnidirectional microphones, it captures voices within a 6-meter radius, ensuring clear communication.



FEATURES



BLUETOOTH & USB TYPE-C PLUG N PLAY

6 meters pick-up range, support USB-C connection and Bluetooth connection



4 OMNIDIRECTIONAL MICROPHONES

Hear and be heard with a 360-degree microphone that picks up sounds from any angle



INNOVATIVE UX DESIGN

Boasts sleek touch buttons, while its LCD screen presents essential information such as battery power, Bluetooth connectivity, speaker volume, and microphone sensitivity



8000MAH (BUILT-IN LITHIUM BATTERY)

Music time (up to 14hours); Battery life(call) up to 24 hours; Fastest Charge time: 3 hours, Regularly 6 hours;
(Support PD2.0/3.0 charging with maximum power up to 18W)



HD VOICE/WIDEBAND AUDIO

HD Voice offers you life-like, vibrant conversations. You will not have to struggle to hear from others



HIGH COMPATIBILITY

It can work with most video conference applications and UC platforms, simply plug and play. To enjoy video conference immediately



TECH SPECIFICATIONS

Product Type	USB / Bluetooth Speakerphone
Bluetooth	BT5.0
Battery	8000mAh (Built-in lithium battery); Music time (up to 14hours); Battery life(call) up to 24 hours; Fastest Charge time: 3 hours, Regularly 6 hours;(Support PD2.0/3.0 charging, with maximum power up to 18W)
Connection type	USB/Bluetooth/Wireless/3.5mm Jack
Sensitivity	-29dBFS
Meeting room size	161 - 323 ft ² (15 - 30m ²)
Meeting with	Up to 15 attendees
Pickup range	6 meters (19.68 feet)
Mics	4x Professional Mics Array
Microphone type	Omni-directional (360 degree pickup range)
Microphone sensitivity	-27dBFS
Noise reduction	Yes
Full duplex audio	Yes
AEC	Yes
Frequency range	100Hz to 22kHz
Speaker	5W/120dB
Interface	1 x Type-C, 1 x 3.5mm audio port
System requirements	Windows 7/8/10 or above, MacOS 10.7 or above, Chrome OS V29.01547 or above
Application support	Software: Skype, FaceTime, Zoom, Microsoft Teams, Hangouts, OBS and Xsplit, etc.
Work temperature	32 to 122°F / 0 to 50°C
Storage temperature	20% to 85% RH (non-condensing)
Work humidity	8.7" x 7.5" x 2.2" [221mm x190mm x 55mm]
Power supply	USB:5V DC @ 500 mA Maximum
Product size	7.1" x 7.1" x 1.4" / 8.7" x 4.3" x 3.3" 180 x 180 x 34.7mm / 220 x 108 x 83mm (before / after packing)
Product weight	1.4 lbs / 2.1 lbs [0.62KG /0.95 KG] (Net / Gross Weight)



Industry-Leading Warranty & Support

BZBGEAR Pro AV products and Cameras come with a three-year warranty. An extended two-year warranty is available for our Cameras upon registration for a total of five years. We pride ourselves in our Customer Service and seven-days-a-week Tech Support.

