
ADJUSTABLE ALUMINUM GANTRY CRANE - AHA-4-15-8

APPROX WEIGHT:399

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

SPECIAL FEATURES

MODEL NUMBER IS AHA-4-15-8 CAPACITY IS 4.000 LBS. BASE WIDTH IS 54 11/16" MAX OVERALL HEIGHT IS 109 1/4" I-BEAM HEIGHT IS 10" I-BEAM FLANGE WIDTH IS 4 11/16" **OVERALL I-BEAM LENGTH IS 180"** USABLE I-BEAM LENGTH IS 156 1/4" ADJUSTABLE UNDER I-BEAM HEIGHT 69 1/4" MIN 99 1/4" MAX HEIGHT IS ADJUSTABLE IN 6" INCREMENTS CASTERS: (4) Ø8" X 3" WIDE PHENOLIC SWIVEL CASTERS WITH FOUR LOCKING POSITIONS CRANE MAY BE TAKEN APART AND BUNDLED WITH

ALUMINÚM CONSTRUCTION

(2) INCLUDED STRAPS FOR EASY TRANSPORT

NONE

DIMENSION TOLERANCE ± 1/4" I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION Ρ Ρ COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS R UNITS REQUIRING APPROVAL DRAWINGS OR 0 MODIFIED ARE NON-RETURNABLE [] As drawn [] As marked Signed: Date: Printed Name: LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING
DISTRIBUTOR'S NAME:

P \(\text{P} \) # W.O.# X VESTIL MANUFACTURING DRAWN BY: ND DATE: 03/25/11 SALES: X reference: X SCALE: 1:34 FILE NAME: Quoted lead time: $_{
m Y}$ QUOTF # 28-007-229

Χ