
ADJUSTABLE ALUMINUM GANTRY CRANE - AHA-6-15-8

APPROX WEIGHT: 856 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

SPECIAL FEATURES
NONE

MODEL NUMBER IS AHA-6-15-8 CAPACITY IS 6,000 LBS. BASE WIDTH IS 64 11/16"

BASE WIDTH IS 64 11/16

MAX OVERALL HEIGHT IS 110"

I-BEAM HEIGHT IS 12"

I-BEAM FLANGE WIDTH IS 7"

OVERALL I-BEAM LENGTH IS 180"

USABLE I-BEAM LENGTH IS 156 1/4"

ADJUSTABLE UNDER I-BEAM HEIGHT

74" MIN

98" MAX

HEIGHT IS ADJUSTABLE IN 6" INCREMENTS

CASTERS: (4) Ø8" X 3" WIDE PHENOLIC

SWIVEL CASTERS WITH FOUR

LOCKING POSITIONS

CRANE MAY BE TAKEN APART AND BUNDLED WITH

(2) INCLUDED STRAPS FOR EASY TRANSPORT

ALUMINUM CONSTRUCTION

	D	IMENSION TOLE	RANCE ± 1	/4"	
A P P R O V	REPRESE REQUIREMI CON COMPLIAN AND LO ANY MODI	PERSIGNED, AGR NTED SATISFIES D ENTS. I ALSO AC NFIRM PRODUCT NCE WITH ALL AF DCAL REGULATION FIED UNITS A	ESIGN AND KNOWLEDG AND INSTA PPLICABLE F DNS AND S' ARE NON-	D DIMENSION GE MY DUTY TO LLLATION EDERAL, STATE TANDARDS. RETURNABLE	Ξ.
Ā	Signed:			Date:	
L	Printed Name		PT OF SIGNE	N APPROVAL DRAW	ING

DATE: 05/21/09

QUOTE #

Χ

DISTRIBUTOR'S NAME:

DRAWN BY: ND

Quoted lead time: $_{
m Y}$

reference: X

VESTIL MANUFACTURING

P.O.# X

W.O.# X

SALES: X

28-007-261

SCALE: 1:40 FILE NAME: