


# MANUAL SCISSOR CART, CART-23-10-M

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING



## STANDARD FEATURES

MODEL NUMBER: CART-23-10-M

CAPACITY: 1,000 LBS.

PLATFORM WIDTH: 24"

PLATFORM LENGTH: 36"

PLATFORM LOWERED HEIGHT: 11"

PLATFORM RAISED HEIGHT: 33 1/2"

OVERALL WIDTH: 36"

OVERALL LENGTH: 58 7/8"

CASTERS: TWO 4 X 2 PHENOLIC SWIVEL W/ BRAKE

TWO 4 X 2 PHENOLIC RIGID

TWO SPEED MANUAL FOOT PUMP:

-AUTOMATIC SHIFT @ 800 - 1000 PSI  
WHEN LOADED.

PRODUCTION WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

SWIVEL W/ BRAKE CASTERS

RIGID CASTERS

REMOVABLE HANDLE

All graphics provided are for reference only. If certain dimensions are critical please verify those dimensions with your salesperson

**A P P R O V A L**

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN & DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT & INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS & STANDARDS.

**UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE**  
( ) As drawn ( ) As marked

Signed: \_\_\_\_\_ Date: \_\_\_\_\_  
Printed Name: \_\_\_\_\_

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

## SPECIAL FEATURES

NONE

\*\*SPECIAL UNITS ARE NON-RETURNABLE  
\*AVAILABLE AT ADDITIONAL COSTS

DISTRIBUTOR'S NAME: <b>VESTIL MFG</b>		P.O.#: -
DRAWN BY: _____		W.O.#: -
DATE: -	SCALE: -	SALES: -
REFERENCE: -	QUOTED LEADTIME: -	DRWG./FILE NAME: CART-23-10-M
QUOTE #:		