
CYLINDER CADDY - CYL-TRUCK-6

APPROX WEIGHT: 212.65 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE



Ρ

Ρ

R

0

٧

Α

DIMENSION TOLERANCE ± 1/4"

STANDARD FEATURES

MODEL NUMBER IS CYL-TRUCK-6 OVERALL WIDTH IS 38 1/4" OVERALL LENGTH IS 52 9/16" **OVERALL HEIGHT IS 36 3/8"** FORK TRUCK MOVEABLE **HOLDS 6 CYLINDERS** Ø9 1/2" MAX CYLINDER DIAMETER MAXIMUM CAPACITY IS 800 LBS INCLUDES (2) Ø4" x 1 1/4" MAROON DURATOUGH POLY SWIVEL W/ BRAKE CASTERS (2) Ø4" x 1 1/4" MAROON DURATOUGH POLY **RIGID CASTERS** TOUGH BAKED IN POWDER COATED

SPECIAL FEATURES

NONE

BLUE FINISH

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE

	[] As diawii	[] As marked	
Signed:		Date:	

Printed Name:

	LE	-AD	TIME	WILL	START	UPON	<i>I RECE</i>	<u>IPT OF</u>	- SIGN	ED A	<i>PPRC</i>	<u> IVAL</u>	<u>DRA</u>	WIN
STRI	BUT	OR'S	NAM	:						Р	.0.# 、	,		

LEAD TIME WILL START UI	PON RECEIP	OF SIGNED	<u>APPROVAL DRAWING</u>
DISTRIBUTOR'S NAME:			P.O.# X
VESTIL MANUFAC	W.O.# X		
	DATE: 3/2 ^s	9/14	SALES: X
EFERENCE: X	,	SCALE: 1:20	
QUOTED LEAD TIME: X	QUOTE#		33-007-265