

DRUM DOLLY - DRUM-DP-LD-55-BU

APPROX WEIGHT: 22.82 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON






MODEL NUMBER IS DRUM-DP-LD-55-BU OVERALL DIAMETER IS ϕ 24 1/4" INNER DIAMETER IS ϕ 23 5/8" OVERALL HEIGHT IS 8 5/16" MAX CAPACITY IS 300 LBS MADE FROM HIGH DENSITY POLYETHYLENE HARD RUBBER 3" CASTERS COLOR IS SAFETY BLUE, MUNSELL - 2.5PB 3.5/10 WORKS WITH 55 OR 30 GALLON DRUMS

SPECIAL FEATURES

NONE



		DIMENSION 1	OLERANCE ± 1/4"
A P R	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE		
0 V	[] As d	rawn [] As ma	arked
A	Signed:		Date:
	Printed Name:		
			X W O #
drawn by: KGH		DATE: 8/24/20016	SALES: X
REFERENCE: X SCALE: 1:12 FILE NAME:			
QUO.	TED LEAD TIME: X	QUOTE #	31-007-255-001