
## MOBILE DRUM DOLLY - DRUM-DRH-HR

APPROX WEIGHT: 24.49 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

\*\*\*ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE\*\*\*



P

P

R

0

V

Α

DIMENSION TOLERANCE ± 1/4"

## STANDARD FEATURES

MODEL NUMBER IS DRUM-DRH-HR **OVERALL DIAMETER IS 30 7/8" USABLE DIAMETER IS 23 1/2" OVERALL HEIGHT IS 6 1/4"** HANDLE LENGTH IS 36' MAX CAPACITY IS 1000 LBS QTY 4- Ø 3" X 1 1/4" SWIVEL HARD RUBBER CASTERS

## SPECIAL FEATURES

**NONE** 

I	, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS
	REPRESENTED SATISFIES DESIGN AND DIMENSION
R	EQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO
	CONFIRM PRODUCT AND INSTALLATION
	COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE
	AND LOCAL REGULATIONS AND STANDARDS.
	NAME OF THE PROPERTY OF THE PR

[ ] As drawn

## ANY MODIFIED UNITS ARE NON-RETURNABLE

[ ] As marked

Signed:	Date:	
D: ( 1N)		

Printed Name:

LEAD TIME WILL START UP	UN RECEIF	TOF SIGNED.	APPROVAL DRAWING
DISTRIBUTOR'S NAME:	P.O.# <b>X</b>		
VESTIL MANUFAC	W.O.# <b>X</b>		
DRAWN BY: KGH	DATE: 5/3	/16	SALES: X
reference: X		SCALE: 1:12	
QUOTED LEAD TIME: X	QUOTE #		33-007-321