



Specifications

Model # DRUM-LRT-II
 Capacity: 550 lbs.
 Lift height: 62"
 Mast: Single
 Safety Shield: Yes
 Overall mast height: 82 5/8"
 Steering wheel: Ø7 x 2"
 Front wheel: Ø5.9x1 1/4"
 Hydraulic Hand Pump
 Number of pumps to raise the drum to maximum height:
 71 pumps
 Number of turns to rotate the drum 360°: 42
 Down Time: 24.28 secs.
 Gear Ratio: 1:42

VESTIL MANUFACTURING CORP.	
DRAWN BY:TM	DATE: 05/17/12
DRWG./FILE NAME:DRUM-LRT-II	
Description: Manual Drum Lifter/Rotator with pivoting adjustable legs	