
ELECTRIC HYDRAULIC SCISSOR LIFT TABLE - EHLT-4048-4-43-QS

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS EHLT-4048-4-43-QS PLATFORM WIDTH IS 40 3/8" PLATFORM LENGTH IS 48 3/8" **OVERALL LENGTH IS 51"** PLATFORM RAISED HEIGHT IS 43" PLATFORM LOWERED HEIGHT IS 7" TABLE CAPACITY (EVENLY DISTRIBUTED) LOAD IS 4.000 LBS CONTROLS HAND PENDANT ON 8' CORD SAFETY MAINTENANCE PROPS, DISPLACEMENT STYLE CYLINDERS INSTALLED ROD DOWN EMERGENCY SAFETY STOP HYDRAULIC FUSES IN ALL CYLINDER UNITS HAVE 2' TEST LEAD AND PIG TAIL

DURABLE LIQUID PAINT BLUE FINISH INTERNAL POWER UNIT

SPECIAL FEATURES

NONE

DECK TOLERANCE ± 1/2" TABLE HEIGHT TOLERANCE ± 1/2" DECK FLATNESS ± 1/4"

0

PI FASE CIRCLE SPECIFICATIONS!

•				U, L	. •	, •		0,10	
	POWER	AC		- DC	DC (12V)			AIR/OIL	
	MOTOR V	OLTA	GE	115	200	}	230-	460	
	DEDICATED CIRCUIT REQUIRED 60Hz								
	MOTOR P	R PHASE SII			NGLE -		THREE		
	CONTR	:OL	I	HANE)		FOC)	

DIMENSION TOLERANCE ± 1/4"

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS

UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE

[] As drawn [] As marked

Signed:	Date:
Printed Name	

<u> </u>	ON RECEIPT OF SIGNEL	<u>) APPROVAL DRAWIN</u>
DISTRIBUTOR'S NAME:		P.O.# X
VESTIL MANUFAC	W.O.# X	
DRAWN BY: BCN	DATE: 3/16/2019	SALES: X
REFERENCE: X	SCALE: 1:14	FILE NAME:
QUOTED LEAD TIME: χ	QUOTE #	24-007-631