
## LOW PROFILE 90° SELF DUMPING HOPPER- H-33-MD

APPROX WEIGHT: 216.22 lbs.

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\* ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



\*\* ADDITION OF CASTERS MAY CHANGE WEIGHT CAPACITY **BASED ON CASTER RATING** 

## STANDARD FEATURES

APPROX. WEIGHT/LOST LOAD=216.22 LBS.

EFFECTIVE THICKNESS= FORK LENGTH MINUS 21 3/4"

MODEL NUMBER: H-33-MD **OVERALL WIDTH: 27"** OVERALL LENGTH: 48 1/4"

**OVERALL HEIGHT: 22 7/16"** CAPACITY: 4,000 LBS.

VOLUME: 1/3 CU. YRD.

TOUGH BAKED IN POWDER COATED BLUE FINISH

## SPECIAL FEATURES

NONE

FOR INTERNAL USE ONLY PROJECT SIGN OFF **SALES** ENG. FAB. POWER

R

0

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS

UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE [ ] As marked [ ] As drawn

Date: Signed:

**Printed Name:** 

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING
DISTRIBUTOR'S NAME:

P.O.# ...

Χ

**VESTIL MANUFACTURING** W.O.#

SALES: X DATE: 9/29<u>/2020</u> JWW

reference: X SCALE: 1:16 FILE NAME: QUOTED LEAD TIME: X QUOTE #

37-007-148