
LOW PROFILE 90° SELF DUMPING HOPPER - H-75-MD

APPROX WEIGHT: 303.34 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***
ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



APPROX. WEIGHT/ LOST LOAD=303.34 LBS.
EFFECTIVE THICKNESS= FORK LENGTH MINUS 21 3/4"

** ADDITION OF CASTERS MAY CHANGE WEIGHT CAPACITY BASED ON CASTER RATING STANDARD FEATURES

LOAD CENTER RATING.

MODEL NUMBER: H-75-MD

EXCEED FORK TRUCK MANUFACTURER'S

OVERALL WIDTH: 27"

OVERALL LENGTH: 56 7/16" OVERALL HEIGHT: 38 11/16"

CAPACITY: 4,000 LBS. VOLUME: 3/4 CU. YRD.

TOUGH BAKED IN POWDER COATED BLUE FINISH

SPECIAL FEATURES

NONE

FOR INTERNAL USE ONLY PROJECT SIGN OFF
SALES
ENG.

FAB.

DISTRIBUTOR'S NAME:
VESTIL MA
DRAWN BY:
JWW
REFERENCE: X
QUOTED LEAD TIME: X

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.

UNITS REQUIRING APPROVAL DRAWINGS OR

MODIFIED ARE NON-RETURNABLE

[] As drawn [] As marked

Signed:_____Date:____

Printed Name:

LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

VESTIL MANUFACTURING

DRAWN BY: JWW

REFERENCE: X

P.O.# X

W.O.# X

PATE: 9/29/2020

SALES: X

REFERENCE: X

QUOTE #

Χ

37-007-151