
## SHORTY LIFT MASTER BOOM, TELESCOPING - LMS-EBT-46-8

APPROX WEIGHT: 443.12 lbs. DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

32"

24" FORK POCKET

\*\*\* ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE \*\*\* ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



## \*--MAXIMUM SINGLE HOOK CAPACITIES

DISTANCE	31"	37''	43''	52''	64''	76 1/2"	89"	A
CAPACITY	8000	7600	7200	6610	5825	5010	4200	P

## STANDARD FEATURES

MODEL NUMBER IS LMS-EBT-46-8 CAPACITY IS 8.000 LBS. **OVERALL WIDTH IS 32"** FORK POCKET CENTERS IS 24" OVERALL LENGTH (RETRACTED) IS 53 7/8" OVERALL LENGTH (EXTENDED) IS 90 7/8" **OVERALL HEIGHT IS 15"** USABLE FORK POCKET IS 2 1/4" X 7 1/4" 31" MINIMUM HOOK POINT 89" MAXIMUM HOOK POINT FRAME DURABLE LIQUID PAINT BLUE FINISH BOOM DURABLE LIQUID PAINT YELLOW FINISH

## SPECIAL FEATURES NONE

APPROX. WEIGHT / LOST LOAD = 443.12 MINIMUM EFFECTIVE THICKNESS = LESS THAN 1" NEVER EXCEED LOAD CENTER RATING PER FORKTRUCK MANUFACTURERS GUIDELINES. DO NOT USE THIS FORK TRUCK ATTACHMENT IF LOAD WILL EXCEED FORK TRUCK MANUFACTURER'S LOAD CENTER RATING

_ V CI	4 11/16" 'ERTICAL ENTER OF GRAVITY	3" 7 1/4" 7 1/4" 16 CEN OF GR DIMENSI	ITER	NCE ± 1/4"					
A P P R O V A L	COMPLIANCE WITH AND LOCAL REC UNITS REQUIRIN MODIFIED [ ] As c Signed: Printed Name:	Isfies desig So ackno Oduct an All Appli Gulations <b>IG Appro</b> <b>ARE NOI</b> Irawn	GN AND DIMENS OWLEDGE MY D ID INSTALLATION CABLE FEDERAL, S AND STANDARI <b>OVAL DRAWI</b> N-RETURNAB [ ] As marked Date	NON UTY TO STATE DS. <b>NGS OR LE</b>					
Image: Lead time will start upon receipt of signed approval drawing   DISTRIBUTOR'S NAME: P.O.# X									
	estil manufac	-	G w.o.#	Х					
DRAW	<sup>in by:</sup> BCN	DATE: 8/22	2/2016 SALES:						
	ENCE: X ED LEAD TIME: X	S QUOTE #	CALE: 1:18 FILE NA	ME: 07-212					
	LD LEAD HIME. X	X		0/-212					