## S - CB - 118 (COUNTER BALANCE STACKER) Specifications Model Number: S-CB-118 Capacity (UDL): 1,000 lbs. up to 62" Capacity (UDL): 500 lbs. 62" to 118" Lift height: 118" Lowered height: 2" Raise speed (un-loaded): 16 secs Raise speed (loaded): 19 secs Down speed (un-loaded): 33 secs Down speed (loaded): 31 secs Adjustable Forks Width of each fork: 3 1/8" Size of each fork (WxTxL): 3 1/8x1 3/16x 30" Fork's range: 6 1/4" - 23 5/8" Mast: Double Safety Shield: YES Overall Mast Height: 78" Drive wheel: Ø10x3 1/8" OVERALL HEIGHT OF CARRIAGE WHEN FORKS ARE FULLY RAISED: 3556mm (140.00") **₽**§ Drive wheel: Ø10x3 1/8" Front wheel: Ø6 1/4x2 3/8" Handle: CH-2 1980mm (78") 1290mm (50<sup>7/8"</sup>) 760mm (30") Q 820mm (32 1/4") 30mm (1 3/16") — 1090mm (43") 30mm (1 3/16") -1359mm (53½") 160-600mm 6 1/4 -23 1/2" R1270 (R50) 600mm (23 5/8") 539mm (21 1/4") - 1359mm (53½") VESTIL MANUFACTRUING CO. DRAWN BY: TM DATE:02/24/11 DRWG./FILE NAME: Reference: S-CB-118