


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022112172](#)
Status: **Active**
Overview: [KK Interconnect Systems](#)
Description: KK 254 Solid Header, Vertical, with Friction Lock, 17 Circuits, Gold (Au) Plating

Documents:

| | |
|--|--|
| 3D Model (PDF) | Packaging Specification PK-6373-001-000 (PDF) |
| Drawing (PDF) | Symbol Footprint Data SYM-22-23-2171-001 (PDF) |
| 3D Model | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-10-07-001 (PDF) | |



Series image - Reference only

Agency Certification

| | |
|-----|---------|
| CSA | LR19980 |
| UL | E29179 |

General

| | |
|----------------|---|
| Product Family | PCB Headers |
| Series | 6373 |
| Application | Signal, Wire-to-Board |
| Overview | KK Interconnect Systems |
| Product Name | KK 254 |
| Taxonomy | PCB Headers and Receptacles |
| UPC | 800753625495 |

Physical

| | |
|--------------------------------|---------------------------|
| Breakaway | No |
| Circuits (Loaded) | 17 |
| Circuits (maximum) | 17 |
| Color - Resin | Natural (White) |
| Durability (mating cycles max) | 50 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Glow-Wire Capable | No |
| Guide to Mating Part | No |
| Lock to Mating Part | Yes |
| Material - Metal | Brass |
| Material - Plating Mating | Gold |
| Material - Resin | Nylon |
| Net Weight | 1.948/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| PC Tail Length | 3.56mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.60mm |
| Packaging Type | Bag |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | No |
| Shrouded | Partial |
| Stackable | No |
| Temperature Range - Operating | See Product Specification |
| Termination Interface: Style | Through Hole |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 4.0A |
|-------------------------------|------|

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[6373 Series](#)

Mates With

[2695](#) , [6471](#) , [7880](#) , [4455](#) , [7720](#)

Voltage - Maximum 500V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-free Process Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 235

Material Info

Engineering Number A-6373-17A241

Reference - Drawing Numbers

Packaging Specification PK-6373-001-000
Product Specification PS-10-07-001
Sales Drawing SD-6373-001-000, SD-6373-001-002
Symbol/Footprint Data SYM-22-23-2171-001

This document was generated on 10/14/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION