

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0191640080**
Status: **Active**
Overview: Perma-Seal Terminals
Description: Perma-Seal Ring Tongue Terminal for 8 AWG Wire, Stud Size 10 (M5)

Documents:

3D Model [Product Specification PS-19902-011-001 \(PDF\)](#)
3D Model (PDF) [Product Specification PS-19902-013-001 \(PDF\)](#)
Drawing (PDF) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series 19164
 Crimp Quality Equipment Yes
 Overview Perma-Seal Terminals
 Product Name Perma-Seal
 Taxonomy Ring and Spade Terminals
 Type Ring
 UPC 800753113640

Physical

Barrel Type Closed
 Insulation NiAc
 Material - Plating Mating Tin
 Net Weight 1.460/g
 Packaging Type Bag
 Stud Size 10 (M5)
 Wire Insulation Diameter 9.53mm
 Wire Size AWG 8
 Wire Size mm² 7.96

Material Info

Engineering Number SD-656-10

Reference - Drawing Numbers

Product Specification PS-19902-011-001, PS-19902-013-001
 Sales Drawing SD-19164-023-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)10043-DC (17
 Jan 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19164 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

PremiumGrade Hand [640013900](#)

Crimp Tool for 2-8

AWG Terminals

Hand Crimp Tool

[640018200](#)

for Perma-Seal

Terminals and Butt

Splices, 8 AWG