

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0643212011](#)
Status: **Active**
Overview: CMC and CMX Sealed, Hybrid, Modular Connectors
Description: .635mm, 1.50mm, 2.80mm, CMC Receptacle, 53 Circuits, Right Wire Output, Black Coding, Mat Sealed

Documents:

3D Model	Application Specification AS-64318-002-SP-001 (PDF)
Drawing (PDF)	Application Specification AS-98420-001-001 (PDF)
3D Model (PDF)	Application Specification AS-98420-001-CH-001 (PDF)
Product Specification PS-64321-001-001 (PDF)	Application Specification AS-98420-001-FR-001 (PDF)
Application Specification AS-64318-002-001 (PDF)	Application Specification AS-98420-001-SP-001 (PDF)
Application Specification AS-64318-002-CH-001 (PDF)	Packaging Specification PK-98995-001-001 (PDF)
Application Specification AS-64318-002-FR-001 (PDF)	RoHS Certificate of Compliance (PDF)

Application tooling part link

Application Tooling Part Link 63812-1100
 Application Tooling Part Link 63824-1200

General

Product Family Crimp Housings
 Series [64321](#)
 Application Automotive, Power, Wire-to-Board
 Comments Current tested on a fully loaded connector, current for temperature increase of 40°C; Current max = 21.0A for 2.80mm Terminal (5.00mm² wire), 12.0A for 1.50mm Terminal (2.00mm² wire), 2.5A for 0.635mm Terminal (0.75mm² wire)


[More Detailed Tech Information](#)

Overview

Product Name [CMC and CMX Sealed, Hybrid, Modular Connectors](#)
 Taxonomy CMC
 UPC Connector Housings 883906135201

Physical

Circuits (maximum) 53
 Circuits Detail 5x 2.8mm, 8 x 1.5mm, 40 x 0.635mm terminals
 Color - Resin Black
 Gender Receptacle
 Glow-Wire Capable No
 Keying to Mating Part Yes
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 50.860/g
 Number of Rows 5
 Packaging Type Carton
 Panel Mount No
 Pitch - Mating Interface 2.54mm, 3.50mm, 7.00mm
 Polarized to Mating Part Yes



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 D(2022)4187-DC (10
 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series

[64321 Series](#)

Mates With

53-Circuit CMC Header [989971002](#) . 154-Circuit CMC Header [347630001](#)

Use With

CMC CP Female Terminal [64322](#) (0.635mm), [64323](#) (1.50mm) . CMC Wire Cap [643211101](#) . Sealing Plugs [643251010](#) , [643251023](#) , [643251091](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Continuity Test Pen Assembly	638121100
Unlocking Tool for CMC and	638241200

Stackable
Temperature Range - Operating

No
-40° to +125°C

CMX Receptacle
Connector

Electrical

Current - Maximum per Contact

12.0A, 2.5A, 21.0A

Solder Process Data

Lead-free Process Capability

N/A

Material Info

Reference - Drawing Numbers

Application Specification

AS-64318-002-001, AS-64318-002-CH-001,
AS-64318-002-FR-001, AS-64318-002-SP-001,
AS-98420-001-001, AS-98420-001-CH-001,
AS-98420-001-FR-001, AS-98420-001-SP-001

Packaging Specification

PK-98995-001-001

Product Specification

PS-64321-001-001

Sales Drawing

SD-64321-001-001

This document was generated on 10/20/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION