

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0731160074**
Status: **Active**
Overview: RF Connectors, RF Cable Assemblies and RF Components
Description: MCRF-to-Pigtail, 0.81mm Cable Diameter, Length 76.2mm, H18, 50 Ohms, One Piece Per Bag

Documents:

| | |
|--|---|
| Drawing (PDF) | Application Specification AS-33472-100-CH-001 (PDF) |
| Product Specification PS-160074-0001-001 (PDF) | RoHS Certificate of Compliance (PDF) |
| Application Specification AS-33472-100-001 (PDF) | |



General

| | |
|------------------------|--|
| Product Family | Cable Assemblies |
| Series | 73116 |
| Assembly Configuration | Single Ended Connector |
| Connector to Connector | MCRF-to-Pigtail |
| Overview | RF Connectors, RF Cable Assemblies and RF Components |
| Product Name | MCRF, RF |
| Taxonomy | RF Cable Assemblies |
| Type | RF Cable Assembly |
| UPC | 884982813618 |

Physical

| | |
|---------------------------|------------------|
| Cable Length | 76.20mm (3.000") |
| Circuits (Loaded) | 0 |
| Gender | Plug-Pigtail |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Gold |
| Material - Resin | Polyester |
| Number of Rows | 1 |
| Packaging Type | Bag |
| Single Ended | Yes |
| Wire/Cable Type | Coaxial |

Electrical

| | |
|-----------|-----|
| Impedance | 50Ω |
|-----------|-----|

Material Info

Reference - Drawing Numbers

| | |
|---------------------------|---------------------------------------|
| Application Specification | AS-33472-100-001, AS-33472-100-CH-001 |
| Product Specification | PS-160074-0001-001 |
| Sales Drawing | SD-73116-007-001 |

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

73116 Series

Mates With

734120110 MCRF, 50 Ohm, Receptacle