

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0732520092](#)
Status: **Active**
Overview: Precision Compression-Mount Microwave Test Connectors
Description: 50 Ohms, Precision Test Connector, 2.92mm PCB Jack, Field Replaceable, 2 Hole Flange, without Screws

Documents:

[Drawing \(PDF\)](#)
[HFSS Model](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	RF/Coax Connectors
Series	73252
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	2.92mm
Style	PCB
Taxonomy	RF / Coaxial Connectors
Type	Subminiature
UPC	884982956001
Wire/Cable Type	N/A

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	None
Net Weight	1.848/g
Orientation	Straight
PCB Mounting	Surface Mount
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	Compression
Reverse Polar	No

Electrical

Frequency	40 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-73252-009-000
---------------	------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[73252 Series](#)