

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936000065](#)  
**Status:** **Active**  
**Overview:** [GWconnect Heavy Duty Connectors \(HDC\)](#)  
**Description:** [GWconnect Metal Gable Gland - 5 Bar, for 30.00-38.00mm Cable, Pg42 Thread](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93600</a>
Cable Gland Type	IP68 - 5 Bar
IP Rating	IP68
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	Cable Glands
Product Name	GWconnect
Taxonomy	Heavy-Duty Cable Glands
UPC	887191829876

**Physical**

Cable Diameter	30.00-38.00mm
Flammability	UL 94V-0
Material - Cable Gland	Brass
Material - Plating	Nickel
Net Weight	313.000/g
Packaging Type	Bag
Panel Cutout Diameter	54.50mm
Panel Mount	Yes
Temperature Range - Operating	-40° to +125°C
Thread Size	Pg42
Thread Type	(Pg)
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP68

**Material Info**

Engineering Number	7000.6897.0
--------------------	-------------

**Reference - Drawing Numbers**

Sales Drawing	936000065-000
---------------	---------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[93600 Series](#)

**Use With**

Industrial connector hoods and housings