

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010437](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Crimp Contact Insert, Female, 4-Pole-40A and 2-Pole-10A, for Crimp Contacts, Size QD

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size QD
 Component Type Inserts - Crimp Contact
 Insert Series S-QD4/2
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard CSA C22.2 NO. 182.3, Desina ISO23570-1, EN 60664-1, EN 61984, UL 1977
 Taxonomy Heavy-Duty Connectors
 UPC 887191890456

Physical

Durability (mating cycles max) 500
 Flammability UL 94V-0
 Gender Female
 Insert Color Grey
 Material - Insert Polycarbonate
 Net Weight 11.000/g
 Number of Rows 3
 Packaging Type Bag
 Polarized to Mating Part Yes
 Poles 6
 Temperature Range - Operating -40° to +125°C

Electrical

Current - Maximum per Contact 16.0A, 4px40A+2px10A
 Voltage - Maximum 250V / 400V / 690V

Material Info

Engineering Number 7606.5815.0



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2022)4187-DC (10
 June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[93601](#) Series

Mates With

[936010438](#) Male Crimp Contact Insert

Use With

Turned Contacts - Female