

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010508](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Crimp Contact Power Module, Female, 2-Pole, 70A, for Crimp Contacts, Grey

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E249674

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Type	Power Module
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Taxonomy	Heavy-Duty Connectors
UPC	887191825649

Physical

Color - Resin	Grey
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Female
Material - Housing	Polycarbonate
Net Weight	10.000/g
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	2
Temperature Range - Operating	-40° to +125°C

Electrical

Current - Maximum per Contact	70.0A
Voltage - Maximum	1000V

Material Info

Engineering Number	7702.3181.0
--------------------	-------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93601](#) Series

Mates With

[936010509](#) Male Power Module

Use With

70.0A Turned Female Crimp Contacts