

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010530](#)  
**Status:** **Active**  
**Overview:** [GWconnect Heavy Duty Connectors \(HDC\)](#)  
**Description:** [GWconnect Crimp Contact Insert, Male, 4-Pole, 40A, for Crimp Contacts, Size «34.2x14.60»](#)

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
 Series [93601](#)  
 Component Size «34.2x14.6»  
 Component Type Inserts - Crimp Contact  
 Insert Series S-M40/3/4  
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)  
 Product Category Heavy Duty Connectors  
 Product Name GWconnect  
 Standard CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977  
 Taxonomy Heavy-Duty Connectors  
 UPC 887191829678

**Physical**

Durability (mating cycles max) 500  
 Flammability UL 94V-0  
 Gender Male  
 Insert Color Grey  
 Material - Insert Polycarbonate  
 Net Weight 12.000/g  
 Number of Rows 2  
 Packaging Type Bag  
 Polarized to Mating Part Yes  
 Poles 4  
 Temperature Range - Operating -40° to +125°C

**Electrical**

Current - Maximum per Contact 40.0A  
 Voltage - Maximum 830V

**Material Info**

Engineering Number 7704.3270.0



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/71/2019 (16 July 2019)

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[93601](#) Series

**Mates With**

[936010529](#) Female Crimp Contact Insert

**Use With**

Turned Contacts - Male