

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010534](#)
Status: **Active**
Overview:
Description: GWconnect Spring Terminal Insert, Male, 5-Pole, 16A, Silver (Ag) Plated Contacts, Size «34.2x14.6»

Agency Certification

UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size «34.2x14.6»
 Component Type Inserts - Spring Terminal
 Insert Series S-M16/5
 Overview hdc_heavy_duty_connectors
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977

Taxonomy

UPC Heavy-Duty Connectors
 887191830452

Physical

Durability (mating cycles max) 500
 Flammability UL 94V-0
 Gender Male
 Insert Color Grey
 Material - Contact Copper Alloy
 Material - Insert Polycarbonate
 Material - Plating Silver
 Net Weight 16.520/g
 Number of Rows 2
 Packaging Type Bag
 Polarized to Mating Part Yes
 Poles 5
 Stripping Length 9.00mm
 Temperature Range - Operating -40° to +125°C
 Wire Size AWG 14-26
 Wire Size mm² 0.14-2.50

Electrical

Current - Maximum per Contact 16.0A
 Voltage - Maximum 400V

Material Info

Engineering Number 7705.3362.0

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601](#) Series

Mates With

[936010533](#) Female Crimp Contact Insert

Use With

Series S-M Frames