

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936011221](#)

**Status:** **Active**

**Overview:** GWconnect Heavy Duty Connectors (HDC)

**Description:** GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 10A «49x16», Extended M25 Threaded Fitting, High Construction, Grey

**Documents:**

[3D Model](#)

[Drawing \(PDF\)](#)

[3D Model \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA 256883  
UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
Series [93601](#)  
Component Size 10A «49X16»  
Component Type Single Lever Hood  
IP Rating IP66  
Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)  
Product Category Heavy Duty Connectors  
Product Name GWconnect  
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984  
Taxonomy Heavy-Duty Connectors  
Type STD  
UPC 887191878287

**Physical**

Entry Location Side  
Hood Coating Polyester Powder  
Hood Color GREY RAL 7037  
Lock to Mating Part Yes  
Material - Hood Die-cast Aluminum  
Material - Peg Stainless Steel  
Net Weight 139.000/g  
Number of Pegs 2  
Packaging Type Bag  
Thread Size M25  
Thread Type (M) Metric

**Electrical**

Voltage - Maximum 500V

**Material Info**

Engineering Number 7810.4582.0

**Reference - Drawing Numbers**

Sales Drawing 936011215-000



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

**China RoHS**

**Search Parts in this Series**

[93601 Series](#)

**Use With**

Size 10A «49x16» S-A and S-D Inserts