

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936012379](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** GWconnect STD - Standard, Double Locking Cover, Die-cast Aluminum, with 2 Levers, with Gasket, Size 16B «77x27», Grey

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA 256883  
 UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
 Series [93601](#)  
 Comments With nylon wire tether line.  
 Component Size 16B «77X27»  
 Component Type Cover  
 IP Rating IP66  
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)  
 Product Category Heavy Duty Connectors  
 Product Name GWconnect  
 Taxonomy Heavy-Duty Connectors  
 Type STD  
 UPC 887191887340

**Physical**

Cover Coating Polyester Powder  
 Cover Color Grey RAL 7037  
 Lock to Mating Part Yes  
 Material - Cover Die-cast Aluminum  
 Material - Lever Stainless Steel  
 Net Weight 104.600/g  
 Number of Levers 2  
 Packaging Type Bag

**Electrical**

Voltage - Maximum 500V

**Material Info**

Engineering Number 7816.5125.0

**Reference - Drawing Numbers**

Sales Drawing 936012379-000



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[93601 Series](#)

**Use With**

Size 16B «77x27» Inserts with 2 Levers