

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936014689](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Single Lever Coupler, Polyamide, with 1 Lever, Top Entry, with Cable Gland, Size «32x13», Pg21 Thread, Black

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size «32X13»
 Component Type Single Lever Coupler
 IP Rating IP66, IP67
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
 Taxonomy Heavy-Duty Connectors
 Type STD
 UPC 887191843018

Physical

Cable Diameter 11.00-18.00mm
 Entry Location Top
 Flammability UL 94V-0
 Gland Color Black RAL 9005
 Hood Color Black RAL 9005
 Lock to Mating Part Yes
 Material - Cable Gland Polyamide
 Material - Hood Polyamide
 Material - Lever Polyamide
 Net Weight 42.000/g
 Number of Levers 1
 Packaging Type Bag
 Thread Size Pg21
 Thread Type (Pg)

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7908.6668.1



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601 Series](#)

Use With

Size «32x13» S-QD Inserts