

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936040037](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Enclosure, Die-cast Aluminum, S-8000 Series, with External Mounting Flanges, 307 x 257 x 121mm Outside Dimensions, Grey RAL 9006

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|------------------|--|
| Product Family | Industrial Connectors / Enclosures |
| Series | 93604 |
| IP Rating | IP66, IP69 |
| Overview | GWconnect Heavy Duty Connectors (HDC) |
| Product Category | Die-cast Enclosures |
| Product Name | GWconnect |
| Standard | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 60670-1, EN 62208, EN-60670-22, NMX-J235/1-2 |
| Taxonomy | Die-cast Enclosures |
| Type | STD |
| UPC | 887191869629 |

Physical

| | |
|-------------------------------|-------------------|
| Enclosure Coating | Polyester Powder |
| Enclosure Color | Grey RAL 9006 |
| Internal Dimensions | 294 x 244 x 114mm |
| Material - Enclosure | Die-cast Aluminum |
| Mounting Style | External Flanges |
| Net Weight | 2375.000/g |
| Outside Dimensions | 307 x 257 x 121mm |
| Packaging Type | Carton |
| Temperature Range - Operating | -40° to +125°C |

Material Info

| | |
|--------------------|-------------|
| Engineering Number | 8000.6266.0 |
|--------------------|-------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2022)4187-DC (10
June 2022)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

Green Image

Not Relevant

Not Contained

CER_4000400780_00_000.pdf

Search Parts in this Series

[93604 Series](#)

Use With

DIN-rails, mounting supports, fixing screws, metal plates, and ground terminals