

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936040047](#)  
**Status:** **Active**  
**Overview:** [GWconnect Heavy Duty Connectors \(HDC\)](#)  
**Description:** [GWconnect Enclosure, Die-cast Aluminum, S-8000 Series, with External Mounting Flanges, 166 x 141 x 137mm Outside Dimensions, Grey RAL 9006](#)

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93604</a>
IP Rating	IP66, IP69
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	Die-cast Enclosures
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 60670-1, EN 62208, EN-60670-22, NMX-J235/1-2
Taxonomy	Die-cast Enclosures
Type	STD
UPC	887191870229

**Physical**

Enclosure Coating	Polyester Powder
Enclosure Color	Grey RAL 9006
Internal Dimensions	154 x 129 x 131mm
Material - Enclosure	Die-cast Aluminum
Mounting Style	External Flanges
Net Weight	833.000/g
Outside Dimensions	166 x 141 x 137mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +125°C

**Material Info**

Engineering Number	8000.6268.0
--------------------	-------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2022)4187-DC (10  
June 2022)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

**China RoHS**

Green Image

Not Relevant

Not Contained

CER\_4000400780\_00\_000.pdf

**Search Parts in this Series**

[93604 Series](#)

**Use With**

DIN-rails, mounting supports, fixing screws, metal plates, and ground terminals

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**