

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936060254](#)  
**Status:** **Active**  
**Overview:** GWconnect Heavy Duty Connectors (HDC)  
**Description:** Gwconnect D-Sub Gender Changer, Female-to-Female. 9 Poles

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93606</a>
Component Type	Gender Changer (D-sub)
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	D-Subs
Product Name	GWconnect
Standard	DIN 41652, IEC 60807
Taxonomy	Heavy-Duty Connectors
UPC	887191846156

**Physical**

Gender	Female-Female
Lock to Mating Part	Yes
Net Weight	11.000/g
Packaging Type	Bag
Poles	9
Temperature Range - Operating	-25° to +125°C

**Electrical**

Current - Maximum per Contact	3.0A
Voltage - Maximum	125V AC / 150V DC

**Material Info**

Engineering Number	2500.0002.0
--------------------	-------------

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/71/2019 (16 July  
2019)

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

**China RoHS**

Green Image

Not Relevant

Not Contained

CER\_4000400784\_00\_000.pdf

**Search Parts in this Series**

[93606](#) Series