

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200650053](#)
Status: **Active**
Overview: Brad Micro-Push M12 Cordsets and Connectors
Description: Micro-Push (M12) Single-Ended Cordset, 4 Poles, Female (Straight)-to-Pigtail, 22 AWG, Unshielded PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
 Series [120065](#)
 Connector End A Micro-Push (M12)
 Connector End B Pigtail
 IP Rating IP65
 Material - Contact Copper Alloy
 Overview [Brad Micro-Push M12 Cordsets and Connectors](#)
 Product Name Micro-Push
 Protocol N/A
 Taxonomy Circular Industrial Cordsets
 Type Single Ended
 UPC 78678850599

Physical

Cable Diameter 4.70mm (.185")
 Cable Length 2.0m (6.56')
 Color - Cable Jacket Black
 Coupling Style Push to Lock
 Gender Female-Pigtail
 Keyway A-coded
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body Nylon
 Material - Coupling Nut N/A
 Material - Plating Mating Gold
 Orientation Straight to Pigtail
 Poles 4
 Temperature Range - Operating -25° to +105°C
 Wire Size AWG 22
 Wire/Cable Type Unshielded PVC

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number N04000A41M020G

Reference - Drawing Numbers

Sales Drawing SD-120065-084-001



EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2022)4187-DC (10
 June 2022)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

Not Relevant

Compliant

Not Contained

CER_4000410036_00_000.pdf

CER_4000410298_00_000.pdf

Search Parts in this Series

[120065 Series](#)

Mates With

Micro-Change M12 Connectors