

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200652261](#)

Status: **Active**

Overview:

Description: Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 3 Poles, Female (90°) to Pigtail, 22 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
 Series [120065](#)
 Connector End A Micro-Change (M12)
 Connector End B Pigtail
 IP Rating IP67
 Material - Contact Brass
 Overview [brad_m8_and_microchange_m12_cordsets_with_knurled_hexnuts_and_wsor_cable](#)
 Product Name Micro-Change (M12)
 Protocol N/A
 Region Europe
 Taxonomy Circular Industrial Cordsets
 Type Single Ended
 UPC 887191554754

Physical

Cable Diameter 4.80mm (.189")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Black
 Coupling Style Knurled Hexnut, Threaded
 Gender Female-Pigtail
 Keyway Single
 LED Indicator No
 Material - Cable Jacket TPU
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold
 Net Weight 141.000/g
 Orientation 90° to Pigtail
 Poles 3
 Temperature Range - Operating -25° to +85°C
 Wire Size AWG 22
 Wire/Cable Type UL 21215

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 60V

Material Info

Engineering Number 803001B30M050

Reference - Drawing Numbers

Sales Drawing 1200656607-000, SD-120065-076-001

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)
 Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS Not Relevant
 ELV Compliant with

Exemption 3

RoHS Phthalates Not Contained

ZZCERT_CE - CER_4000410038_00_000.pdf

Declaration of Conformity

China RoHS

Search Parts in this Series

[120065 Series](#)