

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200655040](#)  
**Status:** **Active**  
**Overview:** Brad Micro-Change (M12) Connectors  
**Description:** Micro-Change (M12) Single-Ended Cordset, 12 Poles, Female (Straight) to Pigtail, 26 AWG, PUR/PVC Cable, 2.0m (6.56') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837

**General**

Product Family Industrial Cordsets  
 Series [120065](#)  
 Connector End A Micro-Change (M12)  
 Connector End B Pigtail  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad Micro-Change \(M12\) Connectors](#)  
 Product Name Micro-Change (M12)  
 Protocol N/A  
 Region Europe  
 Taxonomy Circular Industrial Cordsets  
 Type Single Ended  
 UPC 883906540593

**Physical**


Cable Diameter 6.00mm (.236")  
 Cable Length 2.0m (6.56')  
 Color - Cable Jacket Black  
 Coupling Style Threaded  
 Gender Female-Pigtail  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket PUR/PVC  
 Material - Connector Body PUR  
 Material - Coupling Nut Nickel-plated Brass  
 Material - O-Ring Fluoro-elastomer  
 Material - Plating Mating Gold  
 Orientation Straight to Pigtail  
 Poles 12  
 Temperature Range - Operating -25° to +80°C  
 Wire Size AWG 26  
 Wire/Cable Type UL 20549

**Electrical**

Current - Maximum per Contact 1.5A  
 Voltage - Maximum 30V AC/DC

**Material Info**

Engineering Number 80C000H45M020



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Contained

**Search Parts in this Series**

[120065 Series](#)