

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200660688](#)
Status: **Active**
Overview:
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 22 AWG, Yellow TPE Cable, 1.50m (4.92') Length

Agency Certification

CSA	LR6837
UL	E152210

General

Product Family	Industrial Cordsets
Series	120066
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Brass
Overview	microchange_m12_connectors
Product Name	Micro-Change (M12)
Region	America
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	78678882606

Physical

Cable Diameter	5.30mm (.209")
Cable Length	1.50m (4.92')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	68.038/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-25° to +80°C
Wire Size AWG	22
Wire/Cable Type	PLTC/ITC

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number	884030K05M015
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	1200668165-000, SD-120066-011-001
---------------	-----------------------------------

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

ZZCERT_CE -

CER_4000408918_00_000.pdf

Declaration of

Conformity

ZZCERT_UKCA

CER_4000410285_00_000.pdf

- Declaration of

Conformity

Search Parts in this Series

[120066](#) Series