

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200688193](#)
Status: **Active**
Overview: Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable
Description: Micro-Change (M12) In-Line Splitter with Knurled Hexnuts, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), WSOR Cable, 0.60m (1.97') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Tees and Splitters
 Series [120009](#)
 IP Rating IP67
 Overview [Brad M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable](#)
 Product Name Micro-Change (M12)
 Taxonomy Industrial Tees and Splitters
 Type Splitter - In-line
 UPC 889056131087

Physical

Color - Cable Jacket Black
 Drop Connector N/A
 Drop Gender N/A
 Keyway Single
 LED Indicator No
 Left Trunk Connector Micro-Change (M12)
 Left Trunk Gender Male
 Leg 1 Length 0.60m
 Leg 2 Length 0.60m
 Material - Cable Jacket TPU
 Material - Connector Body TPU
 Material - Coupling Nut Nickel-plated Brass
 Net Weight 81.484/g
 Poles 3 Female/4 Male
 Right Trunk Connector Micro-Change (M12)
 Right Trunk Gender Female
 Temperature Range - Operating -25°C to +80°C

Electrical


Current - Maximum per Contact 4.0A
 Voltage - Maximum 60V

Material Info

Engineering Number 884A30B30M006

Reference - Drawing Numbers

Sales Drawing SD-120068-002-001, SD-120068-002-002



Series image - Reference only

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

50 Image

Compliant with

Exemption 3

Not Contained

CER_4000410542_00_000.pdf

Search Parts in this Series

120009 Series