

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200710034](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (M12) Field Attachable Connector, 5 Poles, Straight, Male, Shielded, Screw Termination, Cable Diameter 6.00-8.00mm

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Field Attachable / Accessories
Series	120071
Approvals	cRUus - UL Recognized
IP Rating	IP67
Material - Contact	Brass
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Taxonomy	Circular Industrial Connectors
Type	Field Attachable Connector
UPC	889056413183

Physical

Cable Diameter	6.00-8.00mm (.236-.315")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	Zinc Die-Cast
Material - Coupling Nut	Brass
Material - Plating Mating	Gold
Net Weight	43.000/g
Orientation	Straight
Poles	5
Temperature Range - Operating	-40°C to +85°C
Wire Size AWG	18

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Material Info

Engineering Number	8A5S06-32
--------------------	-----------

Reference - Drawing Numbers

Sales Drawing	1200710034-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/01/2018 (15 January 2018)
2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000410298_00_000.pdf

Search Parts in this Series

[120071 Series](#)

Mates With

[1200710081](#)