

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200740058](#)
Status: **Active**
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change (1/2" - 20 UNF) US Dual Keyway Receptacle, 3 Poles, 1/4" -18 NPT Mounting Threads, Female (Straight) to 22 AWG PVC Leads, 0.305m (1.0') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Receptacles
 Series [120074](#)
 IP Rating IP67
 NEMA Rating NEMA 6
 Overview [Brad Micro-Change \(M12\) Connectors](#)
 Product Name Micro-Change (1/2" - 20 UNF)
 Taxonomy Circular Industrial Connectors
 Type Single Ended (pigtail)
 UPC 78678822670

Physical

Coupling Type Internal Thread
 Gender Female
 Keyway Dual
 Length 0.305m
 Material - Component Clear Anodized Aluminum
 Mounting Thread Size 1/4" - 18 NPT
 Net Weight 45.000/g
 Orientation Straight
 Panel Mount Front
 Poles 3
 Temperature Range - Operating -20° to +80°C
 Wire Size AWG 22
 Wire/Cable Type UL 1061

Electrical


Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number 7R3A00A19A120

Reference - Drawing Numbers

Sales Drawing SD-120074-014-001



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Compliant with Exemption 6(a),6(b)-II

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

ZZCERT_CE -

CER_4000406200_00_000.pdf

Declaration of

Conformity

ZZCERT_UKCA

CER_4000410292_00_000.pdf

- Declaration of

Conformity

Search Parts in this Series

[120074 Series](#)