

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200795026](#)
Status: **Active**
Overview: Brad Ultra-Lock Connection System
Description: Ultra-Lock (M12) Single-Ended Cordset, 8 Poles, Male (Straight) to Pigtail, 24 AWG, PUR Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Cordsets
 Series [120079](#)
 Connector End A Ultra-Lock (M12)
 Connector End B Pigtail
 IP Rating IP69K
 Material - Contact Copper Alloy
 Overview [Brad Ultra-Lock Connection System](#)
 Product Name Ultra-Lock (M12)
 Protocol EtherNet
 Region Europe
 Taxonomy Circular Industrial Cordsets
 Type Single Ended
 UPC 883906776657

Physical


Cable Diameter N/A
 Cable Length 2.0m (6.56')
 Color - Cable Jacket Black
 Coupling Style Push to Lock
 Gender Male-Pigtail
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PUR
 Material - Connector Body TPE
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold
 Orientation Straight to Pigtail
 Poles 8
 Temperature Range - Operating -20° to +80°C
 Wire Size AWG 24
 Wire/Cable Type N/A

Electrical

Current - Maximum per Contact 2.0A
 Voltage - Maximum 30V

Material Info

Engineering Number W08006H08M020



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120079 Series](#)