

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200840031](#)  
**Status:** **Active**  
**Overview:** Brad Ultra-Lock Connection System  
**Description:** Ultra-Lock (M12) Receptacle, Male (Straight), 5 Poles, M16x1.5 Mounting Threads, PCB Pins, 5.00mm stand-off

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Receptacles
Series	<a href="#">120084</a>
IP Rating	IP69K
NEMA Rating	NEMA 6
Overview	<a href="#">Brad Ultra-Lock Connection System</a>
Product Name	Ultra-Lock (M12)
Taxonomy	Circular Industrial Connectors
Type	PCB Mount
UPC	78172553187

**Physical**

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	N/A
Material - Component	Nickel-plated Brass
Mounting Thread Size	M16 x 1.5
Net Weight	14.806/g
Orientation	Straight
Panel Mount	Back
Poles	5
Temperature Range - Operating	-25° to +90°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

**Material Info**

Engineering Number	WR5U46000
--------------------	-----------

**Reference - Drawing Numbers**

Sales Drawing	SD-120084-170-001
---------------	-------------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

ZZCERT\_UKCA

- Declaration of

Conformity

**China RoHS**

50 Image

Not Relevant

Not Contained

CER\_4000408918\_00\_000.pdf

CER\_4000410285\_00\_000.pdf

**Search Parts in this Series**

[120084 Series](#)