

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200845091](#)  
**Status:** **Active**  
**Overview:** Brad Ultra-Lock Connection System  
**Description:** Ultra-Lock (M12) Receptacle, 12 Poles, Female, M16x1.5 Mounting Threads, PCB Pins, 5.00mm stand-off

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Receptacles
Series	<a href="#">120084</a>
IP Rating	IP69K
NEMA Rating	NEMA 6
Overview	<a href="#">Brad Ultra-Lock Connection System</a>
Product Name	Ultra-Lock (M12)
Taxonomy	Circular Industrial Connectors
Type	PCB Mount
UPC	883906509767

**Physical**

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	N/A
Material - Component	Nickel-plated Brass
Mounting Thread Size	M16 x 1.5
Orientation	Straight
Panel Mount	Back
Poles	12
Temperature Range - Operating	-25° to +90°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

**Electrical**

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V AC/DC

**Material Info**

Engineering Number	WRCU46000
--------------------	-----------

**Reference - Drawing Numbers**

Sales Drawing	SD-120084-051-001
---------------	-------------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120084](#) Series