

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200845192](#)
Status: **Active**
Overview: Brad Ultra-Lock Connection System
Description: Ultra-Lock (M12) Receptacle, 12 Poles, M16x1.5 Mounting Threads, Female (Straight) to 0.34mm² PVC Leads, 0.30m (11.81") Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Receptacles
 Series [120084](#)
 IP Rating IP69K
 NEMA Rating NEMA 6
 Overview [Brad Ultra-Lock Connection System](#)
 Product Name Ultra-Lock (M12)
 Taxonomy Circular Industrial Connectors
 Type Single Ended (pigtail)
 UPC 78172538872

Physical

Coupling Type Internal Thread
 Gender Female
 Keyway Single
 Length 0.30m
 Material - Component Nickel-plated Brass
 Mounting Thread Size M16 x 1.5
 Net Weight 160.000/g
 Orientation Straight
 Panel Mount Back
 Poles 12
 Temperature Range - Operating -25° to +90°C
 Wire Size AWG 26
 Wire/Cable Type Leads, UL 1061

Electrical

Current - Maximum per Contact 1.5A
 Voltage - Maximum 30V AC/DC

Material Info

Engineering Number WRCW40E01C300

Reference - Drawing Numbers

Sales Drawing 1200845189-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c),7(c)-I

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000410038_00_000.pdf

Search Parts in this Series

[120084 Series](#)